














铝合金型材/支架形状一览

铝合金型材

槽宽6mm (5系列) 边长 20 • 40mm   P1837*	 NFS5-2020 HFS5-2020 KNFS5-2020-4000 KHFS5-2020-4000	 NFS5-2040 HFS5-2040 KNFS5-2040-4000 KHFS5-2040-4000	 NFS5-2060 HFS5-2060 KNFS5-2060-4000 KHFS5-2060-4000	 NFS5-4040 HFS5-4040 KNFS5-4040-4000 KHFS5-4040-4000	 HFSF5-2020 KHFSF5-2020-4000	 HFSF5-2020 KHFSF5-2020-4000
槽宽8mm (6系列) 边长 30 • 50 60mm   P1843 P1846	 NEFS6-3030 KNEFS6-3030-4000	 HFS6-3030 KHFS6-3030-4000	 NFSL6-3030 KNFSL6-3030-4000	 NEFSF6-3030 KNEFSF6-3030-4000	 HFSF6-3030 KHFSF6-3030-4000	 NEFSF6-3030 KNEFSF6-3030-4000
	 HFSF6-3030 KHFSF6-3030-4000	 NEFS6-3060 KNEFS6-3060-4000	 HFS6-3060 KHFS6-3060-4000	 NFSL6-3060 KNFSL6-3060-4000	 HFS6-3090 KHFS6-3090-4000	 NEFS6-3090 KNEFS6-3090-4000
	 NEFS6-30120 KNEFS6-30120-4000	 HFS6-5050 KHFS6-5050-4000	 HFS6-50100 KHFS6-50100-4000	 NFS6-6060 HFS6-6060 KNFS6-6060-4000 KHFS6-6060-4000	 NFSR6-3030 KNFSR6-3030-4000	
槽宽10mm (8系列) 边长 40 • 80mm   P1851 P1854	 NEFS8-4040 KNEFS8-4040-4000	 HFS8-4040 KHFS8-4040-4000	 NEFSF8-4040 KNEFSF8-4040-4000	 HFSF8-4040 KHFSF8-4040-4000	 NFSL8-4040 KNFSL8-4040-4000	 NEFSF8-4040 KNEFSF8-4040-4000
	 NFSR8-4040 KNFSR8-4040-4000	 HFSF8-4040 KHFSF8-4040-4000	 NEFS8-4080 KNEFS8-4080-4000	 HFS8-4080 KHFS8-4080-4000	 NFSL8-4080 KNFSL8-4080-4000	 NEFS8-40120 KNEFS8-40120-4000
	 NEFS8-8080 KNEFS8-8080-4000	 HFS8-8080 KHFS8-8080-4000				
槽宽10mm (8-45系列) 边长 45 • 50mm 60 • 90mm   P1859 P1861	 NEFS8-4545 KNEFS8-4545-4000	 HFS8-4545 KHFS8-4545-4000	 NEFSF8-4545 KNEFSF8-4545-4000	 HFSF8-4545 KHFSF8-4545-4000	 NFSL8-4545 KNFSL8-4545-4000	 NEFSF8-4545 KNEFSF8-4545-4000
	 HFSF8-4545 KHFSF8-4545-4000	 NFSR8-4545 KNFSR8-4545-4000	 NEFS8-4590 KNEFS8-4590-4000	 HFS8-4590 KHFS8-4590-4000	 NFSL8-4590 KNFSL8-4590-4000	 NEFS8-5050 KNEFS8-5050-4000
	 NEFS8-50100 KNEFS8-50100-4000	 NFS8-6060 KNFS8-6060-4000	 NFS8-9090 HFS8-9090			
围栏型材 扁型材 P1937 P1944	 HFSFES	 HFSFEW	 HFSFIN5-1020	 HFSFIN5-1044	 HFSFIN5-1074	 HFSFIN5-10104
	 HFSQN4-1020	 HFSQN4-1030	 HFSQN4-1050	 HFSQN4-1070		

支架

[illegible]

接头相关零件

■先装螺帽  P1869	■先装偏心螺帽  P1871
■先装方螺用・金属挡块  P1869	■先装导电螺帽/螺栓  P1869・P1871
■先装螺帽螺栓型  P1871	■长螺帽  P1875・1876
■先装挡块  P1869	■带法兰螺帽  P1876
■先装金属挡块  P1869	■齿形垫圈 (内齿型)  P1876
■后装挡块螺帽  P1874	■铝合金型材用 内六角螺栓  P1877
■后装锁紧螺帽  P1872	■后装隐藏式支架  P1842・1850・1858
■后装螺帽  P1872	■螺丝接头  P1884
■单接头套件 标准型  P1879	■后装螺帽・挡块组件  P1873
■单接头套件 窄型  P1879	