

样品申请邮箱: famarket@misumi.sh.cn

活动时间: 2020年4月6日--2020年6月13日

活动内容: 每家客户仅限5个型号, 且每个型号最多可以申请数量为10个。

*活动对象产品数量有限, 送完即止, 敬请谅解。

直线轴承			
LMUWMF4	SLHFSS3	LHIFRF6	LHFRWF4
SLMUW5	LHMRWF8	LHIFRM6	LHFRWF5
LHFSF5	LHKRL6	LHIFRM10	LHFRWM6
LHFS5	LHMRW6	LHIFRM20	LHFSW4
LHFRW3	SLMU3	LHIFSM6	LHIRW6
LHFRW4	LHFCF3	LHIFSM13	
LHFRWF6	LHFRDM10	SLHFRS3	

轴承座组件			
BGCN624ZZ	C-BGCNB6901ZZ	C-BGCCB6900ZZ	BGRA6204ZZ
BGCN625ZZ	C-BGCNB6002ZZ	C-BGCC608ZZ	BGRA6901ZZ
BGCN6900ZZ	C-BGCRB6900ZZ	C-BGCCB6900ZZ	BGRR605ZZ
BGHK606ZZ-25	C-BGCRB6000ZZ	C-BGCCB6901ZZ	BGRN608ZZ
BGHKA606ZZ-25	C-BGCRB6002ZZ	C-BGCN6902ZZ	BGRN628ZZ
BGRA605ZZ	C-BGCY608ZZ	C-BGCNB6900ZZ	BGBKA606ZZ-20
			C-BGCAB6902ZZ

定位销用衬套			
LCH5-12	JBAN4-6	JBAM12-8	LCBZ15-25
LCH6-10	JBAN6-25	JBAM13-30	JBNM15-25
LCH12-20	JBAN8-15	JBAM20-15	JBAM2-12
LCH12-25	JBAMN3-6	JBAM10-30	JBAM3-8
LCH12-10	JBAMN4-20	JBAM3-7	JBAM13-20
LCHZ8-20	JBAMN6-16	JBHM25-25	JBAM15-20
LCHZ15-20	JBAMN5-5	JBHM25-35	JBAM15-25
LCB6-6	JBHN4-8	JBHM2-6	JBAM15-30
LCB12-25	JBHN13-15	JBHM3-6	JBAM15-16
LCBZ8-8	JBHN15-15	JBHM5-8	JBAM20-16
LCBZ12-20	JBAU5-10	JBHM15-25	JBA16-16
LCBZ8-12	JBAU6-16	JBHM4-20	JBA20-16
LCBZ8-16	JBAU10-10	JBHM2-5	JBA13-10
LCBZ8-20	JBAU13-20	JBHM4-15	JBA5-6
LCBZ10-8	JBAU12-8	JBHM6-15	JBH3-8
LCBZ10-12	JBAU4-16	JBHM6-25	JBH3-10
LCBZ12-25	JBA25-25	JBHM8-15	JBH3-12
LCBZ13-10	JBA2-6	JBAC10-16	JBH4-12
LCBZ15-20	JBA15-30	JBHC8-25	JBH16-16
JBAN5-20	JBAN13-12	JBAN20-20	JBH4-20
JBAN6-8	JBAN13-25	JBAN20-30	JBAN2-6
	JBAN16-25	JBAN25-35	JBAN2-12

固定环			
SCSTR15-15	PSCSW6-10	SSCCN3-8	SSCSM16-12
SCKNK10-10	PSCSW12-12	SSCCN12-12	SSCSM8-8
PSCSJ12-6	PSCSW16-15	SCSBN4-7	PSCSM6-10
SCLSJ25-31	PSCSW18-15	SCSBN40-45	PSCSM8-10
SSCLSJ10-14	SSCSW6-8	SCSBN5-7	PSCSM12-10
PSCSPJ12-6	SSCSW15-10	SCSBN8-14	PSCSM10-12
SSCSPJ16-8	SCSLS40-48	SCSBN20-28	PSCSM15-12
SCS13-10	PSCSLS8-12	SCSBN25-33	PSCSM15-15
SCS18-15	PSCSLS10-14	SCSBN35-45	PSCSM20-10

PSCS8-12	PSCSL30-38	SCSBN40-50	PSCSM20-30
PSCS13-12	PSCSL10-13	PSCSBN10-16	PSCSM25-30
PSCS18-10	PSCSL17-21	PSCSBN12-18	PSCSM30-20
SCSM20-25	PSCSL40-48	PSCSBN12-15	SSCSP15-15
SCSM25-30	SSCSL10-13	PSCSBN25-28	PSCSP10-8
SCSP8-15	SCSG6-8	PSCSBN35-38	SDN13
SCSP4-8	SCSG20-12	PSCSBN35-45	SCCN20-12
SCSP13-12	PSCSG10-12	SSCSBN8-12	SCCN25-18
SCSP10-8	PSCSG30-15	SSCSBN15-18	SCCN30-20
SCST12-12	SSCSG16-10	SCSBS15-19	PSCCN5-6
PSCC6-8	PSCJS25	SCSW15-15	PSCCN20-12

导向轴支座-方/圆			
SHA13	SHAM8	SHAT1320	ATHC4
SHA18	SHAM1320	STHRBN10	SSTHR4
STHS6	SHAM13	STHRN8M	SSTHS5
STHC4	SHSA8-30	SHTBT1020	STHRB8M
SHF3	SHTA12-40	SHTBT1220	STHSB4
ATHR5	SHSTM8-40	SHTBT1320	SHASS10
ATHR13	SHSC10-30	SHTBT2025	SHASS13
ATHS5	SHFML8	SHTBT2530	SHASS16
ATHS6	SHFML13	SHAM815	SHASS2025
		SHAT13	SHASS2030

金属垫圈			
WSF50	WSSS30-16-3	WSSM30-15-3	WSSM20-15-3
WSSB13-4-3	WSSS50-16-5	WSSM6-2-1	WSSB50-12-3
WSSB14-4-3	WSSS10-2-3	WSSM10-6-4	WSSB50-16-5
WSSB14-10-5	WSSS10-2-5	WSSS10-6-5	WSSB60-15-10
WSSB15-10-2	WSSS6-4-1.5	WSSS13-4-1	WSSB60-30-5
WSSB15-12-5	WSSS6-4-5	WSSS13-8-3	WSSB60-30-10
WSSB16-10-3	WSSS5-3-1.5	WSSS14-10-1	WSSB8-2-2
WSSB25-16-5	WSSS15-5-1.5	WSSS20-15-5	WSSB30-25-2
WSSB25-20-3	WSSBH40-12-10	WSSS30-15-2	WSSB6-3-3
WSSB40-20-10	PACK-WSJ6-4-2	WSSS30-15-3	WSSB20-6-6
	WSSM12-3-3	WSSM13-4-2	WSSB20-10-8

同步齿形带			
PTBN200P2M-060	HTUN320S2M-40	TBN200XL037	TBN174XL025
PTBN246P2M-060	HTUN405S3M-60	TBN118XL050	TBN228XL031
HTBN324S2M-100	HTUN591S3M-150	TBN95MXL037	TBN202XL025
HTBN234S3M-60	C-HTBN1752S3M-100	TBN270XL031	TBN154XL031
HTBN255S3M-60	C-HTBN975S5M-250	TBN105MXL025	TBN276XL025
HTBN144S3M-150	C-TTBN1275T5-200	TBN172XL037	TBN166XL037
HTBN177S3M-150	TUN564XL031	TBN228XL050	TBN202XL031
HTBN192S3M-150	TUN180XL037	TBN280XL050	TBN150XL031
HTBN537S3M-150	TUN146XL050	TBN228XL037	TBN310XL031
HTBN710S5M-100	GBN2283GT-90	TBN126XL031	TBN210XL025
HTBN800S8M-150	HTBN234S3M-60	TBN196XL050	TBN182XL025
TTBU630T5-150	HTBN255S3M-60	TBN148XL025	TBN166XL025
TTBU280T5-200	TBN110MXL025	TBN198XL037	TBN370XL025
TTBU295T5-200	HTBN252S3M-60	HTBN288S3M-150	TBN140MXL037
TTBU200T5-250	TBN134XL050	TBN490XL025	TBN460XL031
TTBU225T5-250	HTBN276S3M-60	TBN156XL031	TBN828XL031
TTBU300T5-250	TBN160MXL025	TBN129MXL025	TBN860XL031
TTBU350T5-250	TBN490XL050	TBN82MXL025	TUN94MXL025
TBN330H075	TBN123MXL037	TBN176XL025	TUN106MXL037
TBN420H075	HTBN486S3M-100	TBN90XL050	TUN130MXL037

TBN450H075	TBN460XL050	HTBN324S2M-100	TUN140MXL037
TBN270L050	TBN176XL037	TBN150MXL037	TUN155MXL037
TBN390L050	TBN140MXL025	TBN460XL031	HTUN250S2M-60
TBN420L050	TBN84XL050	TBN160MXL037	HTUN218S2M-40
TBN277L075	TBN124XL037	TBN94XL050	TBN164XL050
TBN322L075	TBN138XL050	TBN97MXL037	TBN180XL050
TBN345L075	TBN396XL037	TBN158XL037	TBN98XL037
TBN480L075	TBN190XL050	TBN240XL025	TBN250XL031
TBN510L075	TBN88MXL025	TBN100MXL037	TBN102XL037
TBN124L100	TBN104XL050	TBN384XL025	TBN320XL050
TBN109L150	TBN188XL050	HTBN456S3M-60	TBN162XL050
TBN124L150	TBN101MXL025	TBN390XL025	TBN162XL031
TBN150L150	TBN396XL050	TBN194XL025	TBN134MXL037
TBN110MXL025	TBN100XL037	TBN340XL031	TBN128XL050
TBN131MXL025	TBN120MXL025	TBN88XL050	TBN424XL025
TBN142MXL025	TBN360XL025	TBN250MXL037	TBN120XL025
TBN160MXL025	TBN490XL037	TBN100XL025	TBN120XL050
TBN63MXL037	HTBN237S3M-60	TBN182XL037	TBN332MXL025
TBN95MXL037	TBN280MXL037	TBN129MXL037	TBN190XL025
TBN132MXL037	TBN630XL037	TBN234XL037	TBN176XL031
TBN134MXL037	TBN228XL025	TBN162XL025	TBN150MXL025
TBN280MXL037	TBN94XL031	TBN124XL031	TBN76XL037
TBN148XL025	TBN63MXL037	TBN118XL025	TBN166XL031
TBN134XL050	TBN152XL050	TBN182XL031	TBN340XL025
TBN176XL025	TBN98XL050	TBN202XL050	TBN94XL031
TBN196XL025	HTBN244S2M-60	TBN156XL037	TBN126XL031
TBN228XL025	TBN435MXL025	TBN370XL050	TBN198XL031
TBN300XL025	TBN210MXL025	TBN162XL037	TBN270XL031
TBN360XL025	TBN390XL050	TBN290XL031	TBN376XL031
TBN376XL025	TBN122XL050	TBN146XL031	TBN396XL031
TBN176XL037	TBN376XL031	TBN200XL025	TBN320XL025
TBN184XL037	TBN124XL050	TBN91MXL025	TBN396XL031
TBN630XL037	TBN236MXL025	TBN154XL025	TBN198XL031
TBN84XL050	TBN210XL037	TBN60XL050	TBN70XL050
TBN94XL050	TBN300XL025	TBN146XL050	HTBN540S3M-60
TBN104XL050	TBN240XL037	TBN142XL031	TBN184XL037
TBN118XL050	TBN196XL025	TBN300XL050	TBN396XL025
TBN152XL050	TBN78XL037	TBN184XL050	TBN148XL031
TBN162XL050	TBN388XL050	TBN170XL031	TBN87MXL037
TBN188XL050	TBN376XL025	TBN300XL031	TBN80XL025
TBN196XL050	TBN131MXL025	TBN140XL037	TBN196XL037
TBN320XL050	TBN132MXL037	TBN390XL031	TBN105MXL037
TBN384XL050	HTBN195S3M-150	TBN134MXL025	
TBN390XL050	TBN384XL050	TBN144XL031	

螺栓			
LVWM30-25	PUSS5-25	SUST6-60	CBSTS10-30
SRMB5-23	PUSS6-45	SUST8-60	CBSTS8-6
SGBSN10-80	PUSS6-50	PUST4-20	CBSM8-8
LVWS24-30	PUSS6-60	PUST10-30	CBSR5-8
LVWS30-25	PUSS8-60	PUST10-40	CBSR5-20
LVBS16-50	PUSS10-70	PUST3-30	CBSR6-16
LVBS10-15	UNAH12-20	PUST6-45	CBSR8-20
ANE8-200	USS10-45	PUST12-30	CBSA8-20
SMSB10-75	USS12-50	PUST12-40	CBSA2-6
MSSG8-45	USTH4-35	USUS4-30	CBSA2-12
CBSTS8-8	USTH8-20	USUS8-50	SGMSB10-60
CBSTS10-16	PSSTH5-40	USUS12-30	DBTB3-10.5-3-LTC

	SUST4-35	SUST4-40	SUST4-30
--	----------	----------	----------

铰链销			
CMG10-30	HCDG4-24	CDG6-40	CLBDG8-40
HCMG3-10	HCDG5-14	CDGH3-22	CLBDG8-50
HCMG3-18	HCDGH3-18	SCDG5-25	CLBDGH12-40
HCMG4-20	HCDGH5-25	SCDG6-18	SCLBDG6-30
HCMG5-12	HCDGH5-30	SCDG6-30	SCLBDG8-20
HCMGH3-12	SHCDG8-16	SCDG8-50	SCLBDG12-35
HCMGH5-20	CLKKH8-40	SCDG10-35	SCLBDG12-45
HCMGH12-24	CLKKH10-50	SCDG10-18	CDG3-24
			CDG10-40

拉伸弹簧用支柱			
ASPO8-50	BSPL6-25	AIPO5-25	ASPL8-25
ASPO8-30	SBSPL3-10	SAIPO10-30	BSPO8-70
ASPO5-40	SAIPOZ5-30	SAIPO5-40	SBSPO3-30
ASPO3-40	PDSP06-25	BSPL3-15	SBSPO4-40
SASPO8-50	SARPO6-30	BSPL5-20	SBSPO8-60
SASPO4-30	SARPO8-35	BSPL5-25	

定位销/定位块			
JPDTA10-14	JPDPA2-3	CJPDPA3-5	CJPDTA6-10
SJPDTA6-8	JPDPA3-5	CJPDPA4-8	CJPDTA12-16
SJPDTA6-10	JPDPA4-6	CJPDPA12-16	CJPDA2-3
CJPDTA6-8	JPDPA4-8	LPN5-30	CJPDA4-8
			CJPDA10-12

螺丝			
LVBM16-15	FSMB8-12	ANHN4-40	SANB20-70
LVBM16-20	FSMB12-40	ANHN20-60	ANBN20-60
ANB3-40	RSM6-16.8	ANHN20-120	SANBN10-30
SANB5-60	RSM8-31.2	STCA4-40	SANBN10-40
SANB12-80	RSM12-22	STCB4-40	SANBN16-70
SANB20-60	RSM8-26.2	FSM8-10	SANBN20-45

金属轴环			
KNCLB3-5-10	KNCLM4-15-20	KNCLM4-10-10	KNCLSS6-20-20
KNCLB16-20-15	KNCLM20-30-15	KNCLM4-10-15	KNCLSS16-20-10
KNCLB6-12-25	KNCLM8-12-35	KNCLM4-14-15	DCLS-D8-V5-H12-T1.5-L11

齿形带金属件			
TBCNL2-4	TBCR-T5150	TBCNL3-15	TBCNL3-6
TBCNL2-6	TBCR-T10150	TBCR-L050	TBCNL3-10
TBCNL2-10	TBCS-S3M060	TBCR-H075	

六角支柱			
BSLCG5.5-15	SLCG5.5-6	SLCB5-15	SLCB5-10
SLCB5-5			

滚轮			
SUMBB15-40	UMBW3-12	UMBH25-65A	SUMBB15-45

止动销			
SSTEHW10	USSTEH13	USSTEH19	

SQNS3-20-12	板螺帽	BMUN2-23	歧管块
CSTFM10	支座	BTLSN5-22	歧管块
FJA4	浮动接头	MBN5-380	聚氨酯圆皮带
NJTW3A	浮动接头	MBN3-236	聚氨酯圆皮带
BNR50	防松动轴承螺帽		
PSFPA20-168-F2-P16-M8-N8-SC100		导向轴	