

**No.ID-2AX CFR**

A 130mm B 1.8mm C 1.0mm



CFR

TIP No.ID-2ACFT



**No.ID-2ABCFR / No.ID-2ABCPR / No.ID-2ABSVR**

A 130mm B 1.8mm C 1.0mm



2ABCFR / CPR

2ABSVR

TIP No.ID-2ABCFT

No.ID-2ABCPT

No.ID-2ABSVT



**No.ID-3CFR**

A 130mm B 0.8mm C 1.3mm



3CFR

TIP No.ID-3CFT



**No.ID-5CFR / No.ID-5CPR / No.ID-5SVR**

A 130mm B 0.5mm C 0.6mm



5CFR

TIP No.ID-5CFT

5CPR

TIP No.ID-5CPT

5SVR

TIP No.ID-5SVT



**No.ID-5XCFR**

A 130mm B 0.5mm C 0.6mm



5XCFR

TIP No.ID-5CFT

**No.ID-7CFR / No.ID-7CPR / No.ID-7SVR**

A 130mm B 0.6mm C 0.6mm



7CFR

TIP No.ID-7CFT

7CPR

TIP No.ID-7CPT

7SVR

TIP No.ID-7SVT



**No.ID-242CFR**

A 130mm B 1.4mm C 1.2mm



242CFR

TIP No.ID-242CFT



**No.ID-246CFR**

A 130mm B 0.6mm C 0.8mm D 9.0mm E 45°



246CFR

TIP No.ID-246CFT

