

形状	型材尺寸	风量 (m ³ /min)												
		0.1	0.2	0.3	0.4	0.5	0.6	0.7	1.0	2.0	3.0	4.0	5.0	
AC风扇 ▶1344页 	80mm边长				25mm 厚									
	92mm边长							25mm 厚						
	120mm边长									25mm 厚	38mm 厚			
DC风扇 •▶1346页 标准型 •带传感器输出 ▶1348页 	40mm边长	10mm 厚												
	60mm边长						25mm 厚							
	80mm边长									25mm 厚				
	92mm边长									25mm 厚				
	120mm边长										38mm 厚			
防水DC风扇 ▶1350页 	40mm边长	10mm 厚												
	80mm边长									25mm 厚				
	92mm边长									25mm 厚				
	120mm边长										38mm 厚			

继电器

开关按钮 ·
指示灯

蜂鸣器

多层信号灯 ·
旋转报警灯

LED灯

开关电源

噪音滤波器

铁氧体磁环

变压器

电路保护器

保险丝

测量仪表

AC/DC风扇

AC电源线

接插件

电源分配器