

伺服马达线束

部品清单

伺服品牌 线束类型	MISUMI线束型号	对应原厂型号	放大器侧		马达侧		A电缆	B电缆	C电缆	D电缆	
			连接器	关联部件	连接器	关联部件					
松下 A6/A5 马达线束 ▶106页	SVPPH-A51	MFMC0A**0RJD	端子	E7508*3 GY RV1-4S*1 RE	SM-JN8FT04S1		20AWG*4C UL2517	20AWG*4C UL2517		20AWG*4C UL2517	
	SVPPH-A52	MFMC0D**2ECD	端子	E2508*3 BU RV2-4S*1 BU	MS3106A20-4S	MS3057-12A	14AWG*4C UL2586	14AWG*4C UL2586		14AWG*4C UL2517	
	SVPPH-A53	MFMC0E**2ECD	端子	E2508*3 BU RV2-4S*1 BU	MS3106A22-22S	MS3057-12A	14AWG*4C UL2586	14AWG*4C UL2586		14AWG*4C UL2517	
	SVPPH-A54	MFMC0A**3ECT	端子	RV5-5*4 YE	MS3106A22-22S	MS3057-12A	12AWG*4C UL2586	12AWG*4C UL2586		12AWG*4C UL2517	
	SVPPH-A55	MFMC0A**0EED	端子	E1008*3 RE RV1-4S*1 RE		172159-1	170362-1	18AWG*4C UL2517	18AWG*4C UL2517		18AWG*4C UL2517
	SVPPH-A51B	MFMC0B**0SJT	端子	RV1-4S*2 RE	JN4FT02SJ1		22AWG*2C UL2464	23AWG*2C UL2464		22AWG*2C UL2517	
	SVPPH-A52B	MFMC0A**2FCD	端子	E2508*3 BU RV2-4S*1 BU RV1-4S*2 RE	MS3106A20-18S	MS3057-12A	14AWG*4C UL2586 18AWG*2C UL2586	14AWG*4C UL2586 18AWG*2C UL2586		14AWG*4C UL2517 18AWG*2C UL2517	
	SVPPH-A53B	MFMC0E**2FCD	端子	E2508*3 BU RV2-4S*1 BU RV1-4S*2 RE	MS3106A24-11S	MS3057-16A	14AWG*4C UL2586 18AWG*2C UL2586	14AWG*4C UL2586 18AWG*2C UL2586		14AWG*4C UL2517 18AWG*2C UL2517	
	SVPPH-A54B	MFMC0A**3FCT	端子	RV5-5*4 YE RV1-4S*2 RE	MS3106A24-11S	MS3057-16A	12AWG*4C UL2586 18AWG*2C UL2586	12AWG*4C UL2586 18AWG*2C UL2586		12AWG*4C UL2517 18AWG*2C UL2517	
	SVPPH-A55B	MFMC0B**0GET	端子	RV1-4S*2 RE	172157-1	170362-1	18AWG*2C UL2517	18AWG*2C UL2517		18AWG*2C UL2517	
	SVPPH-A52AL	-	端子	E2508*3 BU RV2-4S*1 BU	MS3108A20-4S	MS3057-12A	14AWG*4C UL2586	14AWG*4C UL2586		14AWG*4C UL2517	
	SVPPH-A53AL	-	端子	E2508*3 BU RV2-4S*1 BU	MS3108A22-22S	MS3057-12A	14AWG*4C UL2586	14AWG*4C UL2586		14AWG*4C UL2517	
	SVPPH-A54AL	-	端子	RV5-5*4 YE	MS3108A22-22S	MS3057-12A	12AWG*4C UL2586	12AWG*4C UL2586		12AWG*4C UL2517	
	SVPPH-A52BAL	-	端子	E2508*3 BU RV2-4S*1 BU RV1-4S*2 RE	MS3108A20-18S	MS3057-12A	14AWG*4C UL2586 18AWG*2C UL2586	14AWG*4C UL2586 18AWG*2C UL2586		14AWG*4C UL2517 18AWG*2C UL2517	
	SVPPH-A53BAL	-	端子	E2508*3 BU RV2-4S*1 BU RV1-4S*2 RE	MS3108A24-11S	MS3057-16A	14AWG*4C UL2586 18AWG*2C UL2586	14AWG*4C UL2586 18AWG*2C UL2586		14AWG*4C UL2517 18AWG*2C UL2517	
	SVPPH-A54BAL	-	端子	RV5-5*4 YE RV1-4S*2 RE	MS3108A24-11S	MS3057-16A	12AWG*4C UL2586 18AWG*2C UL2586	12AWG*4C UL2586 18AWG*2C UL2586		12AWG*4C UL2517 18AWG*2C UL2517	
松下 A6/A5 编码器线束 ▶108页	SVEPH-A51	MFCEA0**0TJD	SM-6P		SM-JN6FR07SM1		24AWG*2P+22AWG*2C UL20276	24AWG*2P+22AWG*2C UL20276		24AWG*2P+22AWG*2C UL2464	
	SVEPH-A52	MFCEA0**0EOTD	SM-6P		SM-JN2D5T05SL-M		25AWG*3P UL2517	25AWG*3P UL2464		24AWG*3P UL2464	
	SVEPH-A53	MFCEA0**0EAM	SM-6P		172160-1	170361-1	25AWG*3P UL2517	25AWG*3P UL2464		24AWG*3P UL2464	
	SVEPH-A52AL	-	SM-6P		SM-JN2F5T05SL-M		25AWG*3P UL2517	25AWG*3P UL2464		24AWG*3P UL2464	
	SVEPH-A56	MFCEA0**0EAD	SM-6P		172161-1					24AWG	
	SVPPH-MIA41	MFMC0D**2ECT	端子	RV2-4S*4 BU E2508*3 BU RV2-4S*1 BU	MS3106A20-4S	MS3057-12A	14AWG*4C UL2586	14AWG*4C UL2586		14AWG*4C UL2517	
	SVPPH-MIA41S	MFMC0D**2ECD	端子	RV5-5*4 YE RV2-4S*1 BU	MS3106A22-22S	MS3057-12A	12AWG*4C UL2586	12AWG*4C UL2586		12AWG*4C UL2517	
	SVPPH-MIA42	MFMC0A**3ECT	端子	RV5-5*4 YE	MS3106A22-22S	MS3057-12A	12AWG*4C UL2586	12AWG*4C UL2586		12AWG*4C UL2517	
	SVPPH-MIA43S	MFMC0D**2ECD	端子	E2508*3 BU RV2-4S*1 BU	MS3106A20-18S	MS3057-12A	14AWG*4C UL2586	14AWG*4C UL2586		14AWG*4C UL2517	
	SVPPH-MIA44	MFMC0D**3ECT	端子	RV5-5*4 YE	MS3106A24-11S	MS3057-16A	12AWG*4C UL2586	12AWG*4C UL2586		12AWG*4C UL2517	
	SVPPH-MIA45S	MFMC0A**0EED	端子	E1008*3 RE RV1-4S*1 RE		172159-1	170362-1	18AWG*4C UL2517	18AWG*4C UL2517		18AWG*4C UL2517
	SVPPH-MIA41BW	MFMC0A**2FCD	端子	E2508*3 BU RV2-4S*1 BU RV1-4S*2 RE	MS3106A20-18S	MS3057-12A	14AWG*4C UL2586 18AWG*2C UL2586	14AWG*4C UL2586 18AWG*2C UL2586		14AWG*4C UL2517 18AWG*2C UL2517	
	SVPPH-MIA41BSW	MFMC0A**2FCT	端子	RV2-4S*4 BU RV1-4S*2 RE	MS3106A20-18S	MS3057-12A	14AWG*4C UL2586 18AWG*2C UL2586	14AWG*4C UL2586 18AWG*2C UL2586		14AWG*4C UL2517 18AWG*2C UL2517	
	SVPPH-MIA42BW	MFMC0A**3FCT	端子	RV5-5*4 YE RV1-4S*2 RE	MS3106A24-11S	MS3057-16A	12AWG*4C UL2586 18AWG*2C UL2586	12AWG*4C UL2586 18AWG*2C UL2586		12AWG*4C UL2517 18AWG*2C UL2517	
	SVPPH-MIA43B	MFMC0B**0GET	端子	RV1-4S*2 RE	172157-1	170362-1	18AWG*2C UL2517	18AWG*2C UL2517		18AWG*2C UL2517	
	SVPPH-MIA41AL	-	端子	RV2-4S*4 BU	MS3108A20-4S	MS3057-12A	14AWG*4C UL2586	14AWG*4C UL2586		14AWG*4C UL2517	
SVPPH-MIA41SAL	-	端子	E2508*3 BU RV2-4S*1 BU	MS3108A20-4S	MS3057-12A	14AWG*4C UL2586	14AWG*4C UL2586		14AWG*4C UL2517		
SVPPH-MIA42AL	-	端子	RV5-5*4 YE	MS3108A22-22S	MS3057-12A	12AWG*4C UL2586	12AWG*4C UL2586		12AWG*4C UL2517		
SVPPH-MIA43SAL	-	端子	E2508*3 BU RV2-4S*1 BU	MS3108A20-18S	MS3057-12A	14AWG*4C UL2586	14AWG*4C UL2586		14AWG*4C UL2517		
SVPPH-MIA44AL	-	端子	RV5-5*4 YE	MS3108A24-11S	MS3057-16A	12AWG*4C UL2586	12AWG*4C UL2586		12AWG*4C UL2517		
SVPPH-MIA41BVAL	-	端子	E2508*3 BU RV2-4S*1 BU RV1-4S*2 RE	MS3108A20-18S	MS3057-12A	14AWG*4C UL2586 18AWG*2C UL2586	14AWG*4C UL2586 18AWG*2C UL2586		14AWG*4C UL2517 18AWG*2C UL2517		
SVPPH-MIA41BSVAL	-	端子	RV2-4S*4 BU RV1-4S*2 RE	MS3108A20-18S	MS3057-12A	14AWG*4C UL2586 18AWG*2C UL2586	14AWG*4C UL2586 18AWG*2C UL2586		14AWG*4C UL2517 18AWG*2C UL2517		
SVPPH-MIA42BVAL	-	端子	RV5-5*4 YE RV1-4S*2 RE	MS3108A24-11S	MS3057-16A	12AWG*4C UL2586 18AWG*2C UL2586	12AWG*4C UL2586 18AWG*2C UL2586		12AWG*4C UL2517 18AWG*2C UL2517		
松下 A4 编码器线束 ▶116页	SVEPH-MIA41	MFCEA0**0EAM	SM-6P		172160-1	170361-1	25AWG*3P UL2517	25AWG*3P UL2464		24AWG*3P UL2464	
	SVEPH-MIA42	MFCEA0**0EESD	SM-6P		MS3106A20-29S	MS3057-12A	25AWG*3P UL2517	25AWG*3P UL2464		24AWG*3P UL2464	
	SVEPH-MIA42AL	-	SM-6P		MS3108A20-29S	MS3057-12A	25AWG*3P UL2517	25AWG*3P UL2464		24AWG*3P UL2464	
	SVPM-MGK1Y	MR-PWS1CBLJM-A1/ MR-PWS1CBLJM-A2	Y端子 (M3.5)		JN4FT04S1-R	ST-TMH-S-C1B-100(A534G)	NA3CT-18-4			NA3UCSB-18-4	
SVPM-MGK1R	MR-PWS1CBLJM-A1/ MR-PWS1CBLJM-A2	Y端子 (M3.5)		JN4FT04S1-R	ST-TMH-S-C1B-100(A534G)	NA3CT-18-4			NA3UCSB-18-4		
SVPM-MGK1B	MR-PWS1CBLJM-A1/ MR-PWS1CBLJM-A2	丸端子 (M3.5)		JN4FT04S1-R	ST-TMH-S-C1B-100(A534G)	NA3CT-18-4			NA3UCSB-18-4		
SVPM-MGK1RY	MR-PWS1CBLJM-A1/ MR-PWS1CBLJM-A2	Y端子 (M3.5)		JN4FT04S1-R	ST-TMH-S-C1B-100(A534G)	NAVC-21-1P			NAVC-21-1P		
SVPM-MGK1BY	MR-PWS1CBLJM-A1/ MR-PWS1CBLJM-A2	Y端子 (M3.5)		JN4FT04S1-R	ST-TMH-S-C1B-100(A534G)	NAVC-21-1P			NAVC-21-1P		
SVPM-MGK1BR	MR-PWS1CBLJM-A1/ MR-PWS1CBLJM-A2	Y端子 (M3.5)		JN4FT02SJ1-R	ST-TMH-S-C1B-100(A534G)	NAVC-21-1P			NAVC-21-1P		
SVPM-MGK1BR	MR-PWS1CBLJM-A1/ MR-PWS1CBLJM-A2	Y端子 (M3.5)		JN4FT02SJ1-R	ST-TMH-S-C1B-100(A534G)	NAVC-21-1P			NAVC-21-1P		
SVPM-MGK1BR	MR-PWS1CBLJM-A1/ MR-PWS1CBLJM-A2	Y端子 (M3.5)		JN4FT02SJ1-R	ST-TMH-S-C1B-100(A534G)	NAVC-21-1P			NAVC-21-1P		
SVPM-MGK1BR	MR-PWS1CBLJM-A1/ MR-PWS1CBLJM-A2	Y端子 (M3.5)		JN4FT02SJ1-R	ST-TMH-S-C1B-100(A534G)	NAVC-21-1P			NAVC-21-1P		
SVPMH-J3HF1	MR-PWS1CBLJM-A1	号码管*4		JN4FT04S1		20AWG*4C UL2517	20AWG*4C UL2517		20AWG*4C UL2517		
SVPMH-J3HF1R	MR-PWS1CBLJM-A2	号码管*4		JN4FT04S1		20AWG*4C UL2517	20AWG*4C UL2517		20AWG*4C UL2517		
SVPMH-J3HF2	-	号码管*4		MS3106A18-10S	MS3057-10A	16AWG*4C UL2586	16AWG*4C UL2586		16AWG*4C UL2517		
SVPMH-J3HF3	-	号码管*4		MS3106A18-10S	MS3057-10A	14AWG*4C UL2586	14AWG*4C UL2586		14AWG*4C UL2517		
SVPMH-J3HF5	-	号码管*4		MS3106A22-22S	MS3057-12A	14AWG*4C UL2586	14AWG*4C UL2586		14AWG*4C UL2517		
SVPMH-J3HF6	-	号码管*4		MS3106A22-22S	MS3057-12A	10AWG*4C UL2586	10AWG*4C UL2586		10AWG*4C UL2517		
SVPMH-J3HF9	-	号码管*4		MS3106A22-23S	MS3057-12A	14AWG*4C UL2586	14AWG*4C UL2586		14AWG*4C UL2517		
SVPMH-J3HF1B	MR-BKS1CBLJM-A1	号码管*2		JN4FT02SJ1		20AWG*2C UL2464	20AWG*2C UL2464		20AWG*2C UL2517		
SVPMH-J3HF1BR	MR-BKS1CBLJM-A2	号码管*2		JN4FT02SJ1		20AWG*2C UL2464	20AWG*2C UL2464		20AWG*2C UL2517		
SVPMH-J3HF2B	-	号码管*2		SM10-SP25-M		16AWG*2C UL2586	16AWG*2C UL2586		16AWG*2C UL2517		
SVPMH-J3HF2AL	-	号码管*4		MS3108A18-10S	MS3057-10A	16AWG*4C UL2586	16AWG*4C UL2586		16AWG*4C UL2517		
SVPMH-J3HF3AL	-	号码管*4		MS3108A18-10S	MS3057-10A	14AWG*4C UL2586	14AWG*4C UL2586		14AWG*4C UL2517		
SVPMH-J3HF5AL	-	号码管*4		MS3108A22-22S	MS3057-12A	14AWG*4C UL2586	14AWG*4C UL2586		14AWG*4C UL2517		
SVPMH-J3HF6AL	-	号码管*4		MS3108A22-22S	MS3057-12A	10AWG*4C UL2586	10AWG*4C UL2586		10AWG*4C UL2517		
SVPMH-J3HF9AL	-	号码管*4		MS3108A22-23S	MS3057-12A	14AWG*4C UL2586	14AWG*4C UL2586		14AWG*4C UL2517		