

# 伺服马达线束

## 部品清单

伺服品牌 线束类型	MISUMI线束型号	对应原厂型号	放大器侧		马达侧		A电缆	B电缆	C电缆	D电缆
			连接器	关联部件	连接器	关联部件				
三菱 J4・J3・JN 编码器线束 ▶128页	SVEMH-J3HF1	MR-J3ENCLM-A1	SM-10P		1674320-1(A1)		25AWG*3P UL2517	25AWG*3P UL2464		24AWG*3P UL2464
	SVEMH-J3HF1R	MR-J3ENCLM-A2	SM-10P		1674320-1(A1)		25AWG*3P UL2517	25AWG*3P UL2464		24AWG*3P UL2464
	SVEMH-J3HF2	MR-J3ENCLM	SM-10P		SM10-SP10S-M		25AWG*3P UL2517	25AWG*3P UL2464		24AWG*3P UL2464
	SVEMH-J3HF2AL	-	SM-10P		SM10-AP10S-M		25AWG*3P UL2517	25AWG*3P UL2464		24AWG*3P UL2464
	SVEMH-J3HF1M	MR-J3JCL03M-A1	172169-1	170361-1 MTI-002	1674320-1(A1)		25AWG*4P UL2517	25AWG*4P UL2464		24AWG*4P UL2464
	SVEMH-J3HF1RM	MR-J3JCL03M-A2	172169-1	170361-1 MTI-002	1674320-1(A2)		25AWG*4P UL2517	25AWG*4P UL2464		24AWG*4P UL2464
	SVEMH-J3HF1L-D20	MR-EKCBL20M	SM-10P		172161-9	170359-1 MTI-0002	25AWG*6P UL2517	25AWG*6P UL2464		24AWG*6P UL2464
	SVEMH-J3HF1L-D50	MR-EKCBL50M	SM-10P		172161-9	170359-1 MTI-0002	25AWG*6P UL2517	25AWG*6P UL2464		24AWG*6P UL2464
	SVEMH-J3HF2L	MR-J3ENCLM*	SM-10P		SM10-SP10S-M		25AWG*6P UL2517	25AWG*6P UL2464		24AWG*6P UL2464
	SVEMH-J3HF2AL	-	SM-10P		SM10-AP10S-M		25AWG*6P UL2517	25AWG*6P UL2464		24AWG*6P UL2464
	SVPMMH-J2HC1	-	端子	RV1-4S *4 RE	JVT1148-2*2	MXAWG16M-100P	16AWG*4C UL2586	16AWG*4C UL2586		16AWG*4C UL2517
	SVPMMH-J2HC2	-	端子	RV1-4S *4 RE	MS3106A22-23S	MS3057-12A	16AWG*4C UL2586	16AWG*4C UL2586		16AWG*4C UL2517
	SVPMMH-J2HC3	-	端子	RV2-4S *4 BU	MS3106A22-23S	MS3057-12A	14AWG*4C UL2586	14AWG*4C UL2586		14AWG*4C UL2517
	SVPMMH-J2HC4	-	端子	RV5-5 *4 YE	MS3106A24-10S	MS3057-16A	12AWG*4C UL2586	12AWG*4C UL2586		12AWG*4C UL2517
	SVPMMH-J2HC5	-	端子	RV5-5 *4 YE	MS3106A22-23S	MS3057-12A	12AWG*4C UL2586	12AWG*4C UL2586		12AWG*4C UL2517
	SVPMMH-J2HC6	-	端子	RV5-5 *4 YE	MS3106A24-10S	MS3057-16A	10AWG*4C UL2586	10AWG*4C UL2586		10AWG*4C UL2517
SVPMMH-J2HC7	-	端子	RV5-5 *4 YE	MS3106A22-23S	MS3057-12A	10AWG*4C UL2586	10AWG*4C UL2586		10AWG*4C UL2517	
SVPMMH-J2HC1B	-	端子	RV1-4S *6 RE	JVT1148-2*3	MXAWG16M-M-100P	16AWG*6C UL2586	16AWG*6C UL2586		16AWG*4C UL2517 18AWG*2C UL2517	
SVPMMH-J2HC2B	-	端子	RV1-4S *6 RE	MS3106A22-23S	MS3057-12A	16AWG*6C UL2586	16AWG*6C UL2586		16AWG*4C UL2517 18AWG*2C UL2517	
SVPMMH-J2HC3B	-	端子	RV2-4S *4 BU RV1-4S *2 RE	MS3106A22-23S	MS3057-12A	14AWG*6C UL2586	14AWG*6C UL2586		14AWG*4C UL2517 18AWG*2C UL2517	
SVPMMH-J2HC5B	-	端子	RV5-5 *4 YE RV1-4S *2 RE	MS3106A22-23S	MS3057-12A	12AWG*6C UL2586	12AWG*6C UL2586		12AWG*4C UL2517 18AWG*2C UL2517	
SVPMMH-J2HC7B	-	端子	RV5-5 *4 YE RV1-4S *2 RE	MS3106A22-23S	MS3057-12A	12AWG*6C UL2586	12AWG*6C UL2586		12AWG*4C UL2517 18AWG*2C UL2517	
SVPMMH-J2HC8B	-	端子	RV1-4S *6 RE	MS3106A24-10S	MS3057-16A	16AWG*6C UL2586	16AWG*6C UL2586		16AWG*4C UL2517 18AWG*2C UL2517	
SVPMMH-J2HC2AL	-	端子	RV1-4S *4 RE	MS3108A22-23S	MS3057-12A	16AWG*4C UL2586	16AWG*4C UL2586		16AWG*4C UL2517	
SVPMMH-J2HC3AL	-	端子	RV2-4S *4 BU	MS3108A22-23S	MS3057-12A	14AWG*4C UL2586	14AWG*4C UL2586		14AWG*4C UL2517	
SVPMMH-J2HC4AL	-	端子	RV5-5 *4 YE	MS3108A24-10S	MS3057-16A	12AWG*4C UL2586	12AWG*4C UL2586		12AWG*4C UL2517	
SVPMMH-J2HC5AL	-	端子	RV5-5 *4 YE	MS3108A22-23S	MS3057-12A	12AWG*4C UL2586	12AWG*4C UL2586		12AWG*4C UL2517	
SVPMMH-J2HC6AL	-	端子	RV5-5 *4 YE	MS3108A24-10S	MS3057-16A	10AWG*4C UL2586	10AWG*4C UL2586		10AWG*4C UL2517	
SVPMMH-J2HC7AL	-	端子	RV5-5 *4 YE	MS3108A22-23S	MS3057-12A	10AWG*4C UL2586	10AWG*4C UL2586		10AWG*4C UL2517	
SVPMMH-J2HC2BAL	-	端子	RV1-4S *6 RE	MS3108A22-23S	MS3057-12A	16AWG*6C UL2586	16AWG*6C UL2586		16AWG*4C UL2517 18AWG*2C UL2517	
SVPMMH-J2HC3BAL	-	端子	RV2-4S *4 BU RV1-4S *2 RE	MS3108A22-23S	MS3057-12A	14AWG*6C UL2586	14AWG*6C UL2586		14AWG*4C UL2517 18AWG*2C UL2517	
SVPMMH-J2HC5BAL	-	端子	RV5-5 *4 YE RV1-4S *2 RE	MS3108A22-23S	MS3057-12A	12AWG*6C UL2586	12AWG*6C UL2586		12AWG*4C UL2517 18AWG*2C UL2517	
SVPMMH-J2HC7BAL	-	端子	RV5-5 *4 YE RV1-4S *2 RE	MS3108A22-23S	MS3057-12A	12AWG*6C UL2586	12AWG*6C UL2586		12AWG*4C UL2517 18AWG*2C UL2517	
SVPMMH-J2HC8BAL	-	端子	RV1-4S *6 RE	MS3108A24-10S	MS3057-16A	16AWG*6C UL2586	16AWG*6C UL2586		16AWG*4C UL2517 18AWG*2C UL2517	
三菱 J2・J2S 马达线束 ▶134页	SVEMH-J2HC1	MR-JCCBL*M	XDR-10320AS		172161-9	170359-1 MTI-0002	25AWG*5P UL2517	25AWG*5P UL2464		24AWG*5P UL2464
	SVEMH-J2HC2	MR-JHSCBL*M	XDR-10320AS		MS3106A20-29S	MS3057-12A	25AWG*4P UL2517	25AWG*4P UL2464		24AWG*4P UL2464
	SVEMH-J2HC1L	MR-JCCBL*M	XDR-10320AS		172161-9	170359-1 MTI-0002	25AWG*8P UL2517	25AWG*8P UL2464		24AWG*7P UL2464
	SVEMH-J2HC2L	MR-JHSCBL*M	XDR-10320AS		MS3106A20-29S	MS3057-12A	25AWG*8P UL2517	25AWG*8P UL2464		24AWG*6P UL2464
	SVEMH-J2HC2AL	-	XDR-10320AS		MS3108A20-29S	MS3057-12A	25AWG*4P UL2517	25AWG*4P UL2464		24AWG*4P UL2464
	SVEMH-J2HC2LAL	-	XDR-10320AS		MS3108A20-29S	MS3057-12A	25AWG*8P UL2517	25AWG*8P UL2464		24AWG*6P UL2464
	SVPY-SGF71-A	JZSP-C7M10F-□□-E		R1.25-4	J175-06FMH-7KL-M-CF	SJ1F-01GF-P0.8	UL2517 AWG22*6C			
	SVPY-SGF71-B	JZSP-C7M12F-□□-E		R1.25-4	J175-06FMH-7KL-M-CF	SJ1F-01GF-P0.8	UL2517 AWG22*6C			
	SVPY-SGF71R-A	JZSP-C7M10G-□□-E		R1.25-4	J175-06FMH-7KL-M-CF	SJ1F-01GF-P0.8	UL2517 AWG20*6C			
	SVPY-SGF71R-B	JZSP-C7M12G-□□-E		R1.25-4	J175-06FMH-7KL-M-CF	SJ1F-01GF-P0.8	UL2517 AWG22*6C			
SVPY-SGF71B-A	JZSP-C7M13F-□□-E		R1.25-4	J175-06FMH-7KL-M-CF	SJ1F-01GF-P0.8	UL2517 AWG20*6C				
SVPY-SGF71B-B	JZSP-C7M14F-□□-E		R1.25-4	J175-06FMH-7KL-M-CF	SJ1F-01GF-P0.8	UL2517 AWG22*6C				
SVPY-SGF71BR-A	JZSP-C7M13G-□□-E		R1.25-4	J175-06FMH-7KL-M-CF	SJ1F-01GF-P0.8	UL2517 AWG20*6C				
SVPY-SGF71BR-B	JZSP-C7M14G-□□-E		R1.25-4	J175-06FMH-7KL-M-CF	SJ1F-01GF-P0.8	UL2517 AWG22*6C				
SVPY-SGF72-A	JZSP-C7M20F-□□-E		R1.25-4	J275-06FMH-7KL-M-CF	SJ2F-01GF-P1.0	UL2517 AWG20*6C				
SVPY-SGF72R-A	JZSP-C7M20G-□□-E		R1.25-4	J275-06FMH-7KL-M-CF	SJ2F-01GF-P1.0	UL2517 AWG20*6C				
SVPY-SGF72B-A	JZSP-C7M23F-□□-E		R1.25-4	J275-06FMH-7KL-M-CF	SJ2F-01GF-P1.0	UL2517 AWG20*6C				
SVPY-SGF72B-B	JZSP-C7M24F-□□-E		R1.25-4	J275-06FMH-7KL-M-CF	SJ2F-01GF-P1.0	UL2517 AWG22*6C				
SVPY-SGF72BR-A	JZSP-C7M23G-□□-E		R1.25-4	J275-06FMH-7KL-M-CF	SJ2F-01GF-P1.0	UL2517 AWG20*6C				
SVPY-SGF72BR-B	JZSP-C7M24G-□□-E		R1.25-4	J275-06FMH-7KL-M-CF	SJ2F-01GF-P1.0	UL2517 AWG22*6C				
SVPY-SGF73-A	JZSP-C7M30F-□□-E		R1.25-4	J375-06FMH-8KL-M-CF	SJ3F-41GF-P1.8	UL2517 AWG16*4C, 20*2C				
SVPY-SGF73R-A	JZSP-C7M30G-□□-E		R1.25-4	J375-06FMH-8KL-M-CF	SJ3F-41GF-P1.8	UL2517 AWG16*4C, 20*2C				
SVPY-SGF73B-A	JZSP-C7M33F-□□-E		R1.25-4	J375-06FMH-8KL-M-CF	SJ3F-41GF-P1.8/ SJ3F-01GF-P1.8	UL2517 AWG16*4C, 20*2C				
SVPY-SGF73B-B	JZSP-C7M34F-□□-E		R1.25-4	J375-06FMH-8KL-M-CF	SJ3F-41GF-P1.8/ SJ3F-01GF-P1.8	UL2517 AWG16*4C, 20*2C				
SVPY-SGF73BR-A	JZSP-C7M33G-□□-E		R1.25-4	J375-06FMH-8KL-M-CF	SJ3F-41GF-P1.8/ SJ3F-01GF-P1.8	UL2517 AWG16*4C, 20*2C				
SVPY-SGF73BR-B	JZSP-C7M34G-□□-E		R1.25-4	J375-06FMH-8KL-M-CF	SJ3F-41GF-P1.8/ SJ3F-01GF-P1.8	UL2517 AWG16*4C, 20*2C				
安川 Σ7 马达线束 ▶144页	SVEY-SGF71	JZSP-C7P10D-□□-E	55100-0670		504678-0070	56161-8081	UL20276 AWG22*2C, AWG24*2P			
	SVEY-SGF71	JZSP-C7P12D-□□-E	55100-0670		504678-0070	56161-8081	UL20276 AWG22*2C, AWG24*2P			
	SVEY-SGF71R	JZSP-C7P10E-□□-E	55100-0670		504678-0070	56161-8081	UL20276 AWG22*2C, AWG24*2P			
	SVEY-SGF71R	JZSP-C7P12E-□□-E	55100-0670		504678-0070	56161-8081	UL20276 AWG22*2C, AWG24*2P			