

圓形隔板 / 方形隔板

圓形隔板用垫片 / 方形隔板用垫片



■ 圓形隔板

RoHS10

一单孔型—
D=45・55・65・90

φ20
φ13

记号槽(深度2~3mm)
(仅D65・90)

一双孔型—
D=65・80・90

φ20
φ13

3.5

DTMP
DTPME
(高频淬火) (部)

DTPY
DTPYE
(未淬火)

T ± 0.05

材質 S45C

■ 方形隔板

RoHS10

DTPK
(高频淬火) (部)

DTPB
(未淬火)

T ± 0.05

材質 S45C

■ 圓形隔板					
螺栓孔	H	Catalog No.		T	Color
		Type	D		
单孔型	6	DTMP (高频淬火)	45	20	R(红色) Y(黄色) N(标准)
	15			30	
	6			40	
	15			40	
单孔型	15	DTPY (未淬火)	55	30	
	15			40	
	15			30	
	15			40	
单孔型	15	DTPME (高频淬火)	65	30	
	15			40	
	15			30	
	15			40	
双孔型	15	DTPY (未淬火)	90	30	
	15			40	
	15			30	
	15			40	

螺栓孔单孔型的记号槽深度为2~3mm。

Order 订货范例

Catalog No. — B — T — Color (R·Y·N)

DTPME 65 — 30 — R

DTPK 50 — 80 — 30 — N

Delivery 交货期

5 天 发 货

① 上海・广州发货

② 数量≥101时，请另询交货期。

③ 由于圆形隔板可指定颜色、订购方法有变。敬请注意。

以往的订购方式	新的订购方式
DTPK60-80-20	DTPK60-80-20-N

■ 方形隔板 (可指定颜色。)							
H	P	Catalog No.		B	T	Color	
		Type	A				
6	30	DTPK (高频淬火)	38	60	20	R(红色)	
15					30		
6					40		
15	55			80	20		
6					30		
15					40		
6	30		50	60	20		Y(黄色)
15					30		
6					40		
15	55			80	20		
6					30		
15					40		
6	55		60	80	20		N(标准)
15					30		
6					40		
15	70			100	20		
6		30					
15		40					
6	70	80	100	20			
15				30			
6				40			
15	85		120	20			
6				30			
15				40			

Alterations 追加加工

Catalog No. — T — (DC·TC·NMC)

DTPM 65 — 40 — R-DC20

7 天 发 货

① 上海・广州发货

② 数量≥101时，请另询交货期。

Alterations	Code	Spec.
DC	DC	D尺寸单侧切除。 13≤DC<D/2 指定单位1mm ①仅圆形隔板适用
TC	TC	变更板厚(T尺寸)。 (T-5)≤TC<T 指定单位1mm ①DTPM、DTPME、DTPK不适用 ②T=20不适用
NMC	NMC	进行槽加工。 ①仅T=50适用 ②DTPM、DTPME不适用 ③仅圆形隔板适用

■ 圓形隔板用垫片

RoHS10

DTPMS
D=45・55

φ13

D=65・90

3-φ13

φ13

3.5

D=80

2-φ13

3.5

T ± 0.05

材質 SUS304

■ 方形隔板用垫片

RoHS10

DTPKS

T ± 0.05

材質 SUS304

■圆形隔板用垫片

Catalog No.		T
Type	D	
DTPMS	45	0.05
		0.1
		0.2
		0.3
		0.5
		1.0
	55	0.05
		0.1
		0.2
		0.3
		0.5
		1.0
	65	0.05
		0.1
		0.2
		0.3
		0.5
		1.0
	80	0.05
		0.1
		0.2
		0.3
		0.5
		1.0
	90	0.05
		0.1
		0.2
		0.3
		0.5
		1.0

■方形隔板用垫片

P	Catalog No.		B	T
	Type	A		
30	38	50	60	0.05
				0.1
				0.2
				0.3
				0.5
				1.0
			80	0.05
				0.1
				0.2
				0.3
				0.5
				1.0
55	DTPKS	50	60	0.05
				0.1
				0.2
				0.3
				0.5
				1.0
			80	0.05
				0.1
				0.2
				0.3
				0.5
				1.0
30	DTPKS	50	60	0.05
				0.1
				0.2
				0.3
				0.5
				1.0
			80	0.05
				0.1
				0.2
				0.3
				0.5
				1.0
55	DTPKS	50	60	0.05
				0.1
				0.2
				0.3
				0.5
				1.0
			80	0.05
				0.1
				0.2
				0.3
				0.5
				1.0

P	Catalog No.		B	T
	Type	A		
55	60	80	80	0.05
				0.1
				0.2
				0.3
				0.5
				1.0
			100	0.05
				0.1
				0.2
				0.3
				0.5
				1.0
70	DTPKS	80	100	0.05
				0.1
				0.2
				0.3
				0.5
				1.0
			120	0.05
				0.1
				0.2
				0.3
				0.5
				1.0
70	DTPKS	80	100	0.05
				0.1
				0.2
				0.3
				0.5
				1.0
			120	0.05
				0.1
				0.2
				0.3
				0.5
				1.0
85	DTPKS	80	100	0.05
				0.1
				0.2
				0.3
				0.5
				1.0
			120	0.05
				0.1
				0.2
				0.3
				0.5
				1.0

Order
订货范例

Catalog No. — B — T
DTPMS 65 — 0.2
DTPKS 50 — 60 — 0.2

Delivery
交货期

7 天 发 货
● 上海 · 广州 发货
● 数量 ≥ 101 时，
请另询交货期。

Order 订货范例

Catalog No. — B — T

DTPMS 65 — 60 — 0.2

DTPKS 50 — 60 — 0.2

Delivery 交货期

7 天 发 货

① 上海・广州发货

② 数量≥101时，请另询交货期。