

相当于
SKH51
肩部厚度4mm


P·W
—0.01
标准

RECTANGULAR EJECTOR PINS —STANDARD TYPE—

扁推杆
—标准规格—

产品索引

P.37



Order 订货范例
型号 L P W N
CC-ERPH 8-150-P6.0-W1.0-N60

Delivery 交货期
3 天发货

Price 价格
询价联系方式:
WOS: <https://www.misumi-ec.com/cn/> P.19
TEL: 021-6710-8701 / FAX: 021-6710-8687 P.302

Alterations 追加加工
型号 L P W N (AKC·AWC...etc.)
CC-ERPH 8-150-P6.0-W1.0-N60-AKC 0

Alterations	Code	Spec.
	AKC	AKC角度指定单位1° 0 ≤ AKC < 360
	AWC	AWC角度指定单位1° 0 ≤ AWC < 360
	ARC	ARC角度指定单位1° 0 ≤ ARC < 360

Alterations	Code	Spec.
	ADC	ADC角度指定单位1° 0 ≤ ADC < 360
	HC	HC尺寸指定单位0.1mm D+1 ≤ HC < H
	TC	TC尺寸指定单位0.1mm T/2 < TC < T L.N尺寸缩短了(T-TC)

H	T	型号		L	P	W	N	
		Type	D					
3	4	CC-ERPH	4	1.5	100 150	0.8 1.0 1.2	0.3 0.4 0.5 0.6	40~90
								40~140
4	4	CC-ERPH	4	2	100 150 200	1.0 1.2 1.5	0.4 0.5 0.6 0.7 0.8 1.0	40~90
								40~140
5	4	CC-ERPH	4	2.5	100 150 200	1.5 (2.0)	0.4 0.5 0.6 0.7 0.8 1.0 1.2 (1.5)	40~90
								40~140
6	4	CC-ERPH	4	3	100 150 200	2.0 (2.5)	0.4 0.5 0.6 0.7 0.8 1.0 1.2 (1.5) (2.0)	40~90
								40~140
7	4	CC-ERPH	4	3.5	100 150 200 250	2.5 (3.0)	0.4 0.5 0.6 0.7 0.8 0.9 1.0 1.2 1.5 (2.0)	40~90
								40~140
8	4	CC-ERPH	4	4	100 150 200 250	3.0 (3.5)	0.4 0.5 0.6 0.7 0.8 0.9 1.0 1.2 1.5 (2.0)	40~90
								40~140
9	4	CC-ERPH	4	4.5	100 120 150 200 250	3.5 (4.0)	0.6 0.7 0.8 0.9 1.0 1.2 1.5 1.8 (2.0) (2.5)	40~90
								40~140
10	4	CC-ERPH	4	5	100 150 200 250	4.0	0.6 0.7 0.8 0.9 1.0 1.2 1.5 1.8 2.0 2.5	40~90
								40~140
11	4	CC-ERPH	4	5.5	100 120 150 175 200 250	4.5 (5.0)	0.8 0.9 1.0 1.2 1.5 1.8 2.0 (2.5)	40~90
								40~140
12	4	CC-ERPH	4	6	150 200 250	5.0	0.8 0.9 1.0 1.2 1.5 1.8 2.0 2.5 3.0	40~140
								40~190
13	4	CC-ERPH	4	6.5	150 200 250	6.0	0.8 0.9 1.0 1.2 1.5 1.8 2.0	40~140
								40~190
14	4	CC-ERPH	4	7	120 150 175 200 250	6.0	0.8 0.9 1.0 1.2 1.5 1.8 2.0 2.5	40~110
								40~140
15	4	CC-ERPH	4	7.5	150 200 250	6.0	0.8 0.9 1.0 1.2 1.5 1.8 2.0 2.5	40~140
								40~190
16	4	CC-ERPH	4	8	150 200 250	7.0	0.8 0.9 1.0 1.2 1.5 1.8 2.0 2.5	40~140
								40~190
17	4	CC-ERPH	4	8.5	200 250	7.0	0.8 0.9 1.0 1.2 1.5 1.8 2.0 2.5	40~140
								40~190
18	4	CC-ERPH	4	10	150 200 250	8.0	0.8 1.0 1.2 1.5 1.8 2.0 2.5	40~190
								40~240
19	4	CC-ERPH	4	10.5	150 200 250	10.0	1.0 1.2 1.5 1.8 2.0 2.5	40~190
								40~240

不能同时选择P·W尺寸“()”内的数值。

RECTANGULAR
EJECTOR PINS

扁推杆