### DOW CORNING CORPORATION **Material Safety Data Sheet**

Page: 1 of 7

### DOW CORNING(R) SE 4450 THERMALLY CONDUCTIVE ADHESIVE

#### 1. IDENTIFICATION OF THE SUBSTANCE AND OF THE COMPANY

24 Hour Emergency Telephone: (989) 496-5900 **Dow Corning Corporation** South Saginaw Road Customer Service: (989) 496-6000 Midland, Michigan 48686 Product Disposal Information: (989) 496-6315 CHEMTREC: (800) 424-9300 MSDS No.: 02393247 Revision Date: 2002/04/11 Generic Description: Silicone Physical Form: Viscous Liquid Color: Gray Odor: Slight odor NFPA Profile: Health 1 Flammability 1 Instability/Reactivity 0 Note: NFPA = National Fire Protection Association 2. OSHA HAZARDOUS COMPONENTS CAS Number Wt % **Component Name** None > 60.0 Treated aluminum oxide 68037-59-2 <1.0 Dimethyl, methylhydrogen siloxane The above components are hazardous as defined in 29 CFR 1910.1200. 3. EFFECTS OF OVEREXPOSURE Acute Effects Eye: Direct contact may cause temporary redness and discomfort. Skin: No significant irritation expected from a single short-term exposure. Inhalation: Vapor overexposure may cause drowsiness. Oral: Low ingestion hazard in normal use. Prolonged/Repeated Exposure Effects Skin: Repeated or prolonged exposure may cause irritation. Inhalation: No known applicable information. Oral: No known applicable information. Signs and Symptoms of Overexposure No known applicable information. Medical Conditions Aggravated by Exposure

## DOW CORNING CORPORATION Material Safety Data Sheet

Page: 2 of 7

### DOW CORNING(R) SE 4450 THERMALLY CONDUCTIVE ADHESIVE

No known applicable information.

The above listed potential effects of overexposure are based on actual data, results of studies performed upon similar compositions, component data and/or expert review of the product. Please refer to Section 11 for the detailed toxicology information.

4. FIRST AID MEASURE	5		
Eye:	Immediately flush with water.		
Skin:	No first aid should be needed.		
Inhalation:	Remove to fresh air. Get medical attention if ill effects persist.		
Oral:	No first aid should be needed.		
Comments:	Treat according to person's condition and specifics of exposure.		
5. FIRE FIGHTING MEAS	BURES		
Flash Point:	> 212 °F / > 100 °C (Closed Cup)		
Autoignition Temperature:	Not determined.		
Flammability Limits in Air:	Not determined.		
Extinguishing Media:	On large fires use dry chemical, foam or water spray. On small fires use carbon dioxide (CO2), dry chemical or water spray. Water can be used to cool fire exposed containers.		
Fire Fighting Measures:	Self-contained breathing apparatus and protective clothing should be worn in fighting large fires involving chemicals. Use water spray to keep fire exposed containers cool. Determine the need to evacuate or isolate the area according to your local emergency plan.		
Unusual Fire Hazards:	None.		
Hazardous Decomposition Products			
Thermal breakdown of this product during fire or very high heat conditions may evolve the following hazardous decomposition products: Carbon oxides and traces of incompletely burned carbon compounds. Silicon dioxide. Formaldehyde. Metal oxides. Hydrogen.			
6. ACCIDENTAL RELEASE MEASURES			

## DOW CORNING CORPORATION Material Safety Data Sheet

Page: 3 of 7

### DOW CORNING(R) SE 4450 THERMALLY CONDUCTIVE ADHESIVE

Containment/Clean up: Determine whether to evacuate or isolate the area according to your local emergency plan. Observe all personal protection equipment recommendations described in Sections 5 and 8. For large spills, provide diking or other appropriate containment to keep material from spreading. If diked material can be pumped, store recovered material in appropriate container. Materials in contact with water, moisture, acids or bases have the potential to generate hydrogen gas. Recovered material should be stored in a vented container. Clean up remaining materials from spill with suitable absorbant. Clean area as appropriate since some silicone materials, even in small quantities, may present a slip hazard. Final cleaning may require use of steam, solvents or detergents. Dispose of saturated absorbant or cleaning materials appropriately, since spontaneous heating may occur. Local, state and federal laws and regulations may apply to releases and disposal of this material, as well as those materials and items employed in the cleanup of releases. You will need to determine which federal, state and local laws and regulations are applicable. Sections 13 and 15 of this MSDS provide information regarding certain federal and state requirements.

Note: See section 8 for Personal Protective Equipment for Spills. Call Dow Corning Corporation, (989) 496-5900, if additional information is required.

#### 7. HANDLING AND STORAGE

Use with adequate ventilation. Product evolves flammable methyl alcohol when exposed to water or humid air. Provide ventilation during use to control exposure within Section 8 guidelines or use air-supplied or self-contained breathing apparatus. Avoid eye contact. Avoid breathing vapor. Keep container closed.

Product may evolve minute quantities of flammable hydrogen gas which can accumulate. Adequately ventilate to maintain vapors well below flammability limits and exposure guidelines. Do not repackage. Do not store in glass containers which may shatter due to pressure build up. Clogged container vents may increase pressure build up. Keep container closed and store away from water or moisture.

#### 8. EXPOSURE CONTROLS / PERSONAL PROTECTION

#### **Component Exposure Limits**

CAS Number Component Name

Exposure Limits

None Treated aluminum oxide

See methyl alcohol comments.

Methyl alcohol forms on contact with water or humid air. Provide adequate ventilation to control exposures within guidelines of OSHA PEL: TWA 200 ppm and ACGIH TLV-skin: TWA 200 ppm, STEL 250 ppm.

#### **Engineering Controls**

Local Ventilation:	Recommended.
General Ventilation:	Recommended.

#### Personal Protective Equipment for Routine Handling

Eyes: Use proper protection - safety glasses as a minimum.

Skin: Washing at mealtime and end of shift is adequate.

## DOW CORNING CORPORATION Material Safety Data Sheet

Page: 4 of 7

### DOW CORNING(R) SE 4450 THERMALLY CONDUCTIVE ADHESIVE

Suitable Gloves:	No special protection needed.

Inhalation: Use respiratory protection unless adequate local exhaust ventilation is provided or air sampling data show exposures are within recommended exposure guidelines. Industrial Hygiene Personnel can assist in judging the adequacy of existing engineering controls.

Suitable Respirator: General and local exhaust ventilation is recommended to maintain vapor exposures below recommended limits. Where concentrations are above recommended limits as determined by air sampling or are unknown, appropriate respiratory protection should be worn. Follow OSHA Respirator Regulations (29 CFR 1910.134) and use NIOSH/MSHA approved respirators.

#### Personal Protective Equipment for Spills

Eyes: Use full face respirator.

Skin: Washing at mealtime and end of shift is adequate.

Inhalation/Suitable Respiratory protection recommended. Follow OSHA Respirator Regulations (29 CFR 1910.134) and use NIOSH/MHSA approved respirators. Protection provided by air purifying respirators against exposure to any hazardous chemical is limited. Use a positive pressure air supplied respirator if there is any potential for uncontrolled release, exposure levels are unknown, or any other circumstance where air purifying respirators may not provide adequate protection.

Precautionary Measures: Avoid eye contact. Avoid breathing vapor. Keep container closed. Use reasonable care.

Comments: Product evolves flammable methyl alcohol when exposed to water or humid air. Provide ventilation during use to control exposure within Section 8 guidelines or use air-supplied or self-contained breathing apparatus.

Note: These precautions are for room temperature handling. Use at elevated temperature or aerosol/spray applications may require added precautions.

#### 9. PHYSICAL AND CHEMICAL PROPERTIES

Physical Form:Viscous Liquid<br/>Color:Color:Gray<br/>Odor:Specific Gravity @ 25°C:2.7Viscosity:500 PoiseFreezing/Melting Point:Not determined.<br/>Soling Point:Boiling Point:> 35C/95FVapor Pressure @ 25°C:Not determined.<br/>Not determined.<br/>Not determined.<br/>Not determined.<br/>Not determined.<br/>Not determined.Solubility in Water:Not determined.<br/>Not determined.<br/>Not determined.<br/>Not determined.Volatile Content:Not determined.

Note: The above information is not intended for use in preparing product specifications. Contact Dow Corning before writing specifications.

## DOW CORNING CORPORATION **Material Safety Data Sheet**

Page: 5 of 7

### DOW CORNING(R) SE 4450 THERMALLY CONDUCTIVE ADHESIVE

## **10. STABILITY AND REACTIVITY**

Stable.

Chemical Stability:

Hazardous

Hazardous polymerization will not occur. Polymerization:

Conditions to Avoid: None.

Materials to Avoid: Oxidizing material can cause a reaction. Water, alcohols, acidic or basic materials, and many metals or metallic compounds, when in contact with product, liberate flammable hydrogen gas, which can form explosive mixtures in air.

#### **11. TOXICOLOGICAL INFORMATION**

#### **Special Hazard Information on Components**

No known applicable information.

#### **12. ECOLOGICAL INFORMATION**

#### **Environmental Fate and Distribution**

Complete information is not yet available.

#### **Environmental Effects**

Complete information is not yet available.

#### Fate and Effects in Waste Water Treatment Plants

Complete information is not yet available.

Ecotoxicity Classification Criteria					
Hazard Parameters (LC50 or EC50)	High	Medium	Low		
Acute Aquatic Toxicity (mg/L)	<=1	>1 and <=100	>100		
Acute Terrestrial Toxicity	<=100	>100 and <= 2000	>2000		
This table is adapted from "Environmental Toxicology and Risk Assessment", ASTM STP 1179, p.34, 1993,					

9, F

This table can be used to classify the ecotoxicity of this product when ecotoxicity data is listed above. Please read the other information presented in the section concerning the overall ecological safety of this material.

#### **13. DISPOSAL CONSIDERATIONS**

#### RCRA Hazard Class (40 CFR 261)

When a decision is made to discard this material, as received, is it classified as a hazardous waste? Yes

Characteristic Waste: Reactive:

D003

State or local laws may impose additional regulatory requirements regarding disposal.

## DOW CORNING CORPORATION Material Safety Data Sheet

Page: 6 of 7

### DOW CORNING(R) SE 4450 THERMALLY CONDUCTIVE ADHESIVE

Call Dow Corning Corporate Environmental Management, (989) 496-6315, if additional information is required.

#### **14. TRANSPORT INFORMATION**

#### DOT Road Shipment Information (49 CFR 172.101)

Not subject to DOT.

#### **Ocean Shipment (IMDG)**

Not subject to IMDG code.

#### Air Shipment (IATA)

NOT IATA REGULATED. (VENTED PACKAGES FORBIDDEN FOR AIR TRANSPORT)

Call Dow Corning Transportation, (989) 496-8577, if additional information is required. **15. REGULATORY INFORMATION** 

Contents of this MSDS comply with the OSHA Hazard Communication Standard 29 CFR 1910.1200.

TSCA Status: All chemical substances in this material are included on or exempted from listing on the TSCA Inventory of Chemical Substances.

#### EPA SARA Title III Chemical Listings

#### Section 302 Extremely Hazardous Substances:

None.

#### Section 304 CERCLA Hazardous Substances:

None.

#### Section 312 Hazard Class:

Acute: Yes Chronic: No Fire: No Pressure: No Reactive: Yes

#### Section 313 Toxic Chemicals:

None present or none present in regulated quantities.

#### **Supplemental State Compliance Information**

#### California

Warning: This product contains the following chemical(s) listed by the State of California under the Safe Drinking Water and Toxic Enforcement Act of 1986 (Proposition 65) as being known to cause cancer, birth defects or other reproductive harm.

## DOW CORNING CORPORATION Material Safety Data Sheet

Page: 7 of 7

### DOW CORNING(R) SE 4450 THERMALLY CONDUCTIVE ADHESIVE

None known.

#### Massachusetts

No ingredient regulated by MA Right-to-Know Law present.

#### New Jersey

CAS Number	<u>Wt %</u>	Component Name
None	> 60.0	Treated aluminum oxide
68083-19-2	10.0 - 30.0	Dimethyl siloxane, dimethylvinyl-terminated
Pennsylvania		
CAS Number	<u>Wt %</u>	Component Name
None	> 60.0	Treated aluminum oxide
68083-19-2	10.0 - 30.0	Dimethyl siloxane, dimethylvinyl-terminated

#### **16. OTHER INFORMATION**

Prepared by: Dow Corning Corporation

These data are offered in good faith as typical values and not as product specifications. No warranty, either expressed or implied, is hereby made. The recommended industrial hygiene and safe handling procedures are believed to be generally applicable. However, each user should review these recommendations in the specific context of the intended use and determine whether they are appropriate.

(R) indicates Registered Trademark

## **Product Information**

## Thermal Interface -Wet Dispensed

#### **FEATURES**

- Flowable
- Outstanding thermal conductivity values
- Heat Cure
- High tensile strength
- No added solvents

#### **BENEFITS**

- No mixing of separate components required
- Rapid, versatile cure processing controlled by temperature
- Able to flow, fill or self-leveling after dispensing
- Heat flow away from electronic components can increase reliability

#### **POTENTIAL USES**

- Adhesive for power supply components
- Ink jet printer heads
- Bonding ICs with heat sinks

#### **APPLICATION METHODS**

• Automated or manual dispensing



# *Dow Corning*<sup>®</sup> SE 4450 Thermally Conductive Adhesive

1-part gray, flowable thermally conductive adhesive with high tensile strength

#### **TYPICAL PROPERTIES**

Specification Writers: Please contact your local Dow Corning sales office or your Global Dow Corning Connection before writing specifications on this product.

57000 57000 57 2.73 30 94
57000 57 2.73 30 94
57 2.73 30 94
2.73 30 94
30 94
94
1060
7.3
74
45
570
3.9
390
575
22
0.006
0.003
3.3E15
legF 3.322
1.92
6

#### DESCRIPTION

The heat-cure, thermally conductive adhesives produce no by-products in the cure process, allowing their use in deep section and complete confinement. These adhesives will develop good, primerless adhesion to a variety of common substrates including metals, ceramics, epoxy laminate boards, reactive materials and filled plastics. Long-term, reliable protection of sensitive circuits and components is important in many of today's delicate and demanding electronic applications. With the increase in processing power and the trend toward smaller, more compact electronic modules, the need for thermal management is growing. Thermally conductive silicones function as heat transfer media, durable dielectric insulation, barriers against environmental contaminants and as stress-relieving shock and vibration absorbers over a wide temperature and humidity range. In addition to sustaining their physical and electrical properties over a broad range of operating conditions, silicones are resistant to ozone and ultraviolet degradation and have good chemical stability. Good heat transfer is dependent on a good interface between the heat producing device and the heat transfer media. Silicones have a low surface tension that enables them to wet most surfaces, which can lower the thermal contact resistance between the substrate and the material.

#### SUBSTRATE TESTING

To ensure maximum bond strength for adhesives on a particular substrate, 100 percent cohesive failure of the adhesive in a lap shear or similar adhesive strength test is needed. This ensures compatibility of the adhesive with the substrate being considered. Also, this test can be used to determine minimum cure time or to detect the presence of surface contaminants such as mold release agents, oils, greases and oxide films.

#### **PROCESSING/CURING**

Addition-cure adhesives should be cured at 100°C (212 °F) or above. The cure rate is rapidly accelerated with heat (see heat-cure times in Typical Properties table). Thin sections of less than mils may be cured in 15 minutes at 150°C (30 °F). For thicker sections, a pre-cure at 70°C (158°F) may be necessary to reduce voids in the elastomer. Length of pre-cure will depend on section thickness and confinement of adhesive. It is recommended that 30 minutes at 70°C (158°F) be used as a starting point for determining necessary pre-cure time. Addition-curing materials contain all the ingredients needed for cure with no by-products from the cure mechanism. Deep-section or confined cures are possible. Cure progresses evenly throughout the material. These adhesives generally have long working times.

#### **ADHESION**

Dow Corning silicone adhesives are specially formulated to provide unprimed adhesion to many reactive metals, ceramics and glass, as well as to selected laminates, resins and plastics. However, good adhesion cannot be expected on non-reactive metal substrates or non-reactive plastic surfaces such as Teflon®, polyethylene or polypropylene. Special surface treatments such as chemical etching or plasma treatment can sometimes provide a reactive surface and promote adhesion to these types of substrates. Dow Corning® brand primers can be used to increase the chemical activity on difficult substrates. For best results, the primer should be applied in a very thin, uniform coating and then wiped off after application. After application, primers should be thoroughly cured prior to application of the silicone elastomer. Poor adhesion can be experienced on plastic or rubber substrates that are highly plasticized, since the mobile plasticizers act as release agents. Small-scale laboratory evaluation of all substrates is recommended before production trials are made. In general, increasing the cure temperature

and/or cure time will improve the ultimate adhesion.

#### USEFUL TEMPERATURE RANGES

For most uses, silicone adhesives should be operational over a temperature range of -45 to 200°C (-49 to 392 °F) for long periods of time. However, at both the low and high temperature ends of the spectrum, behavior of the materials and performance in particular applications can become more complex and require additional considerations. For low-temperature performance, thermal cycling to conditions such as -55°C (-67°F) may be possible for most products, but performance should be verified for your parts or assemblies. Factors that may influence performance are configuration and stress sensitivity of components, cooling rates and hold times, and prior temperature history. At the high-temperature end, the durability of the cured silicones is time and temperature dependent. As expected, the higher the temperature, the shorter the time the material will remain useable.

#### SOLVENT EXPOSURE

Although highly filled silicones such as those discussed in this data sheet are generally more resistant to solvent or fuel exposure, standard silicones are intended only to survive splash or intermittent exposures. Testing should be done to confirm performance of the adhesives in the application and under the specified environmental conditions.

# STORAGE AND SHELF LIFE

Shelf life is indicated by the "Use By" date found on the product label. For best results, Dow Corning thermally conductive materials should be stored at or below the maximum specified storage temperature. Special precautions must be taken to prevent moisture from contacting these materials. Containers should be kept tightly closed and head or air space minimized. Partially filled containers should be purged with dry air or other gases, such as nitrogen. Any special storage and handling instructions will be printed on the product containers.

#### HEALTH AND ENVIRONMENTAL INFORMATION

To support customers in their product safety needs, Dow Corning has an extensive Product Stewardship organization and a team of Product Safety and Regulatory Compliance (PS&RC) specialists available in each area. For further information, please see our website, www.dowcorning.com, or consult your local Dow Corning representative.

#### LIMITATIONS

These products are neither tested nor represented as suitable for medical or pharmaceutical uses.

#### LIMITED WARRANTY INFORMATION PLEASE READ CAREFULLY

The information contained herein is offered in good faith and is believed to be accurate. However, because conditions and methods of use of our products are beyond our control, this information should not be used in substitution for customer's tests to ensure that Dow Corning's products are safe, effective, and fully satisfactory for the intended end use. Suggestions of use shall not be taken as inducements to infringe any patent. Dow Corning's sole warranty is that the product will meet the Dow Corning sales specifications in effect at the time of shipment. Your exclusive remedy for breach of such warranty is limited to refund of purchase price or replacement of any product shown to be other than as warranted. DOW CORNING SPECIFICALLY DISCLAIMS ANY OTHER EXPRESS OR IMPLIED WARRANTY OF FITNESS FOR A PARTICULAR PURPOSE OR MERCHANTABILITY. DOW CORNING DISCLAIMS LIABILITY FOR ANY INCIDENTAL OR CONSEQUENTIAL DAMAGES.

#### SAFE HANDLING INFORMATION

PRODUCT SAFETY INFORMATION REQUIRED FOR SAFE USE IS NOT INCLUDED IN THIS DOCUMENT. BEFORE HANDLING, READ PRODUCT AND MATERIAL SAFETY DATA SHEETS AND CONTAINER LABELS FOR SAFE USE, PHYSICAL AND HEALTH HAZARD INFORMATION. THE MATERIAL SAFETY DATA SHEET IS AVAILABLE ON THE DOW CORNING WEBSITE AT WWW.DOWCORNING.COM, OR FROM YOUR DOW CORNING REPRESENTATIVE, OR DISTRIBUTOR, OR BY CALLING YOUR GLOBAL DOW CORNING CONNECTION.

#### **For More Information**

To learn more about these and other products available from Dow Corning, please visit the Dow Corning Electronics website at www.dowcorning.com/ electronics.

DOW CORNING

Electronics Solutions

Dow Corning and Sylgard are registered trademarks of Dow Corning Corporation. All other trademarks or brand names are the property of their respective owners. ©2008 Dow Corning Corporation. All rights reserved. Printed in USA Form No. 11-1321B-01