

AVLV2.E173648 - APPLIANCE WIRING MATERIAL - COMPONENT

Appliance Wiring Material - Component

See General Information for Appliance Wiring Material - Component

CABLEPLUS TECHNOLOGIES COMPANY LIMITED
FLAT 28, BLK B, 20/F WAH LOK IND CENTRE, 31 SHAN MEI STREET
FOTAN DISTRICT
SHATIN, NEW TERRITORIES HONG KONG

E173648

Table of Recognized Styles

Single-conductor, thermoplastic insulation.							
1007	1569	1836	10271	10571	10719	10925	11323
1015	1571	1867	10322	10572	10721	10958	11331
1056	1577	1870	10335	10578	10731	10973	11343
1061	1581	1886	10359	10579	10741	10981	11367
1095	1589	1901	10367	10584	10753	10982	11390
1185	1591	1918	10368	10587	10754	10983	11406
1232	1592	1921	10378	10628	10770	10984	11407
1275	1617	1922	10387	10636	10771	10987	11445
1284	1618	1926	10429	10647	10835	10989	11491
1332	1643	1994	10439	10649	10847	11008	11492
1333	1644	10002	10456	10660	10848	11009	11528
1354	1670	10012	10467	10666	10857	11010	11529
1371	1672	10042	10483	10678	10858	11098	11530
1385	1673	10063	10492	10681	10863	11113	11538
1430	1674	10064	10493	10682	10866	11117	11539
1431	1685	10070	10512	10684	10880	11122	11545
1478	1691	10199	10532	10686	10882	11133	11562
1500	1729	10239	10548	10687	10907	11134	11624
1516	1731	10255	10553	10689	10914	11170	11634
1517	1777	10263	10557	10692	10918	11172	11720

1533	1814	10264	10559	10705	10924	11287	
Multiple-conductor, thermoplastic insulation.							
2095	2725	20317	20669	20952	21241	21328	21573
2096	2733	20320	20671	20955	21269	21329	21586
2103	2791	20327	20689	20963	21273	21330	21591
2129	2835	20328	20698	20979	21274	21339	21598
2405	2841	20329	20724	21029	21276	21344	21611
2448	2845	20330	20728	21030	21279	21349	21612
2463	2851	20375	20788	21031	21280	21356	21686
2464	2854	20376	20801	21032	21281	21364	21687
2468	2919	20378	20802	21060	21282	21369	21797
2480	2935	20379	20844	21080	21283	21383	21814
2501	2990	20380	20850	21089	21284	21390	21815
2517	20010	20429	20851	21098	21285	21425	21885
2547	20092	20430	20854	21099	21286	21449	21923
2560	20093	20449	20866	21100	21287	21451	21924
2562	20197	20450	20868	21101	21288	21452	21925
2570	20233	20494	20870	21118	21289	21455	21926
2571	20234	20495	20877	21119	21292	21456	21927
2576	20235	20496	20895	21120	21293	21458	21928
2586	20236	20549	20911	21126	21294	21459	21929
2587	20251	20554	20935	21143	21306	21466	21938
2595	20255	20605	20936	21149	21307	21523	21944
2611	20259	20606	20937	21164	21308	21524	21947
2651	20276	20607	20938	21165	21310	21525	21976
2661	20279	20608	20939	21198	21317	21526	22009
2662	20280	20626	20940	21209	21318	21527	22010
2678	20281	20642	20948	21223	21319	21535	22030
2682	20285	20663	20950	21236	21320	21550	22031
2717	20306	20668	20951	21238	21327	21551	
Single-conductor, thermoset insulation.							
3173	3265	3289	3321	3398	3468	3553	3932
3195	3266	3302	3343	3415	3534	3558	3994

3196	3271	3314	3385	3424	3551	3683	
3199	3288	3315	3386	3456	3552	3781	
Multiple-conductor, thermoset insulation.							
4339	4346	4410	4411	4412	4413	4414	4484

Marking: Company name, voltage rating, temperature rating, conductor size, conductor material if other than copper, and use.

Last Updated on 2019-07-29

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2019 UL LLC"