

【技术计算】传动 同步齿形带的选型方法9
传动容量表

注：本章节中提供的产品参数不适用于经济型同步带产品

表52. EV5GTの基准传动容量 Ps ー皮带公称宽度15mm时ー (W)

小带轮齿数 节圆直径 (mm)	14	16	18	20	22	24	26	28	30	32	36	40	44	48	54	60	72	80
小带轮 转速(rpm)	22.28	25.46	28.65	31.83	35.01	38.20	41.38	44.56	47.75	50.93	57.30	63.66	70.03	76.39	85.94	95.49	114.59	127.32
20	13	18	22	27	33	38	42	47	52	56	64	72	80	87	97	108	128	139
40	24	33	41	50	61	70	79	88	96	104	120	136	150	163	183	203	240	263
60	33	46	58	72	87	100	113	126	139	150	173	196	216	236	264	293	348	380
100	50	71	91	113	136	157	178	199	219	237	273	310	343	374	419	465	552	604
200	85	125	163	205	248	287	326	365	403	438	506	575	636	695	780	867	1031	1129
300	115	173	228	289	350	407	464	520	574	625	723	823	912	996	1119	1244	1482	1623
400	142	217	289	369	447	520	594	667	737	803	931	1060	1176	1285	1445	1607	1914	2096
500	166	258	347	445	539	629	718	808	894	974	1131	1289	1430	1564	1759	1957	2333	2555
600	188	297	402	518	627	733	839	944	1046	1141	1325	1511	1678	1836	2065	2298	2740	3002
700	208	333	454	589	712	834	956	1077	1193	1302	1514	1728	1919	2101	2364	2632	3139	3439
800	227	368	505	657	795	933	1069	1206	1337	1460	1699	1940	2156	2360	2657	2958	3529	3866
870	239	392	540	704	851	1000	1147	1294	1436	1569	1826	2086	2319	2539	2858	3183	3797	4161
900	244	402	554	724	875	1028	1180	1332	1478	1615	1880	2148	2388	2615	2944	3279	3912	4286
1000	260	434	602	789	954	1122	1289	1456	1616	1767	2058	2352	2616	2865	3227	3593	4288	4698
1160	284	483	675	890	1075	1268	1459	1649	1832	2004	2337	2672	2973	3257	3669	4087	4878	5343
1200	289	495	693	915	1105	1304	1500	1696	1885	2062	2405	2751	3061	3353	3778	4209	5023	5502
1400	315	551	780	1035	1251	1478	1704	1929	2145	2349	2742	3138	3493	3828	4314	4807	5736	6282
1450	321	565	801	1065	1286	1521	1754	1986	2209	2419	2825	3233	3599	3945	4446	4954	5912	6474
1600	338	605	863	1152	1391	1647	1901	2155	2397	2627	3070	3516	3914	4291	4837	5390	6430	7040
1750	354	643	923	1237	1494	1771	2046	2320	2583	2831	3311	3793	4224	4631	5221	5817	6939	7595
1800	358	655	943	1264	1527	1811	2093	2374	2644	2899	3390	3884	4326	4743	5347	5958	7106	7777
2000	376	703	1020	1374	1659	1971	2280	2589	2884	3164	3703	4244	4728	5185	5846	6513	7765	8494
2400	406	791	1165	1584	1911	2278	2641	3003	3349	3678	4309	4943	5509	6042	6812	7587	9034	9868
2800	440	872	1301	1783	2151	2571	2986	3400	3795	4171	4892	5615	6259	6865	7737	8613	10238	11165
3200	486	945	1429	1973	2380	2851	3318	3782	4225	4647	5455	6263	6982	7657	8625	9594	11379	12384
3600	529	1011	1550	2155	2598	3120	3636	4150	4640	5107	5998	6888	7679	8419	9477	10531	12456	13522
4000	571	1072	1665	2330	2808	3379	3944	4505	5041	5550	6522	7492	8350	9151	10291	11423	13466	14575
5000	667	1202	1925	2738	3296	3986	4667	5343	5985	6597	7758	8910	9920	10854	12167	13450	15686	16815
6000	700	1305	2153	3108	3737	4539	5330	6112	6853	7559	8889	10199	11335	12372	13803	15172	17429	18431
7000	700	1382	2352	3445	4136	5044	5936	6817	7648	8438	9915	11358	12590	13695	15183	16561	18641	19343
8000	700	2524	3749	4495	5501	6487	7459	8370	9235	10835	12383	13677	14812	16285	17586	17586	19259	
9000	700	2671	4023	4815	5912	6984	8037	9018	9946	11645	13265	14586	15706	17086	18212			
10000	700	4266	5096	6277	7426	8550	9591	10570	12339	13998	15303	16361	17560					
12000	700	4660	5541	6865	8141	9375	10498	11541	13356	14976	16113	16883						
14000	700	4930	5825	7256	8617	9915	11067	12113	13831	15238								

※由于□□□范围内耐久时间会减少，因此请尽可能避免在这一区域内使用。皮带宽度不同时，请乘以表28的宽度补偿系数。

表53. EV8YUの基准传动容量 Ps ー皮带公称宽度20mm时ー (kW)

小带轮齿数 节圆直径 (mm)	20	22	24	26	28	30	32	34	36	38	40	44	48	54	60	64	72	80
	50.93	56.02	61.12	66.21	71.30	76.39	81.49	86.58	91.67	96.77	101.86	112.05	122.23	137.51	152.79	162.97	183.35	203.72
10	0.04	0.04	0.05	0.05	0.05	0.06	0.06	0.07	0.07	0.08	0.08	0.09	0.10	0.12	0.13	0.14	0.16	0.18
20	0.07	0.08	0.09	0.10	0.10	0.11	0.13	0.13	0.14	0.15	0.16	0.18	0.20	0.23	0.26	0.28	0.32	0.36
40	0.13	0.14	0.16	0.18	0.20	0.22	0.24	0.26	0.28	0.30	0.32	0.36	0.40	0.46	0.52	0.56	0.64	0.72
60	0.18	0.21	0.23	0.26	0.29	0.32	0.35	0.38	0.41	0.44	0.48	0.54	0.60	0.69	0.78	0.84	0.96	1.08
100	0.28	0.33	0.37	0.42	0.47	0.52	0.57	0.62	0.67	0.72	0.78	0.88	0.99	1.14	1.30	1.40	1.60	1.80
200	0.52	0.60	0.69	0.79	0.89	0.99	1.10	1.20	1.29	1.39	1.52	1.73	1.96	2.27	2.58	2.79	3.19	3.60
300	0.74	0.86	0.99	1.13	1.29	1.45	1.62	1.76	1.90	2.05	2.25	2.57	2.92	3.38	3.85	4.18	4.78	5.40
400	0.94	1.10	1.28	1.47	1.67	1.89	2.12	2.30	2.50	2.70	2.97	3.40	3.86	4.48	5.12	5.56	6.37	7.20
500	1.13	1.34	1.56	1.80	2.05	2.32	2.61	2.84	3.08	3.33	3.68	4.23	4.81	5.59	6.38	6.94	7.95	8.99
600	1.32	1.57	1.83	2.12	2.42	2.75	3.10	3.38	3.67	3.97	4.38	5.04	5.75	6.68	7.64	8.31	9.53	10.78
700	1.50	1.79	2.10	2.43	2.79	3.17	3.58	3.90	4.24	4.59	5.08	5.86	6.68	7.77	8.89	9.68	11.10	12.57
800	1.68	2.00	2.36	2.74	3.15	3.59	4.05	4.43	4.81	5.22	5.78	6.66	7.61	8.86	10.14	11.04	12.67	14.34
870	1.80	2.15	2.54	2.95	3.40	3.87	4.38	4.79	5.21	5.65	6.26	7.23	8.26	9.62	11.01	11.99	13.76	15.58
900	1.85	2.21	2.61	3.04	3.50	4.00	4.52	4.94	5.38	5.83	6.47	7.47	8.54	9.95	11.39	12.40	14.23	16.11
1000	2.02	2.42	2.86	3.34	3.85	4.40	4.99	5.46	5.94	6.45	7.15	8.27	9.46	11.03	12.63	13.75	15.78	17.88
1160	2.28	2.74	3.26	3.81	4.41	5.05	5.73	6.27	6.83	7.42	8.24	9.54	10.92	12.75	14.60	15.91	18.26	20.68
1200	2.34	2.82	3.35	3.92	4.54	5.20	5.91	6.47	7.06	7.66	8.51	9.86	11.29	13.17	15.09	16.45	18.87	21.37
1400	2.65	3.21	3.83	4.50	5.22	5.99	6.82	7.48	8.16	8.86	9.86	11.43	13.11	15.30	17.54	19.11	21.93	24.83
1450	2.73	3.31	3.94	4.64	5.39	6.19	7.05	7.72	8.43	9.16	10.20	11.82	13.56	15.83	18.15	19.78	22.69	25.68
1600	2.95	3.59	4.29	5.06	5.88	6.77	7.72	8.47	9.24	10.05	11.20	12.99	14.91	17.41	19.96	21.75	24.95	28.23
1750	3.17	3.87	4.63	5.47	6.37	7.34	8.39	9.20	10.05	10.93	12.19	14.15	16.25	18.98	21.75	23.71	27.18	30.75
1800	3.24	3.96	4.75	5.61	6.53	7.53	8.61	9.44	10.31	11.22	12.52	14.54	16.69	19.50	22.35	24.36	27.93	31.58
2000	3.52	4.32	5.19	6.14	7.17	8.29	9.48	10.41	11.37	12.38	13.82	16.06	18.46	21.56	24.71	26.94	30.85	34.86
2400	4.06	5.01	6.05	7.19	8.43	9.76	11.20	12.30	13.45	14.65	16.39	19.07	21.93	25.61	29.34	31.97	36.55	41.21
2800	4.57	5.66	6.88	8.20	9.64	11.20	12.87	14.15	15.48	16.87	18.90	22.00	25.31	29.55	33.82	36.82	41.99	47.22
3200	5.05	6.29	7.67	9.18	10.82	12.59	14.50	15.95	17.46	19.03	21.35	24.86	28.60	33.35	38.12	41.46	47.14	52.83
3600	5.50	6.89	8.43	10.12	11.96	13.95	16.08	17.69	19.38	21.12	23.72	27.62	31.78	37.01	42.22	45.86	51.95	57.98
4000	5.94	7.47	9.17	11.03	13.06	15.26	17.62	19.39	21.23	23.15	26.02	30.30	34.84	40.50	46.10	50.00	56.39	
5000	6.91	8.79	10.87	13.16	15.65	18.34	21.24	23.37	25.59	27.88	31.39	36.50	41.90	48.40	54.68			
6000	7.75	9.94	12.38	15.05	17.97	21.12	24.52	26.95	29.47	32.08	36.16	41.92	47.96	54.90				
7000	8.44	10.92	13.68	16.70	20.00	23.57	27.39	30.06	32.82	35.65	40.22	46.41	52.84					
8000	8.99	11.72	14.76	18.09	21.27	25.63	29.82	32.65	35.55	38.52	43.45							