

扁型材 肩型




CAD文件名例: HFSPURE →pure5851
HFSFIN →fin50104

CAD数据文件名: 37_Aluminum_Frames


请按照选型步骤①～④选择型式和参数后进行订购。

Order 型式 (①Type · ②No. · ③型式) - ④L
订货范例 HFSFIN5-1020 - 1200


■扁型材 肩型



■M5螺帽型



■M6螺帽型



■M8螺帽型



型式	①Type	②No.	③型式	指定単位1mm	質量 kg/m	截面積 mm ²	截面慣性矩mm ⁴	
							ℓx × 10 ⁴	ℓy × 10 ⁴
HFSFIN	5		1020	50～3000	0.36	131	0.12 × 10 ⁴	0.53 × 10 ⁴
			1044		0.55	203	1.70 × 10 ⁴	2.45 × 10 ⁴
			1074		0.99	364	0.32 × 10 ⁴	13.97 × 10 ⁴
			10104		1.42	526	0.46 × 10 ⁴	41.90 × 10 ⁴
		6	1530		0.82	302	0.62 × 10 ⁴	2.85 × 10 ⁴
			1554		1.01	374	0.78 × 10 ⁴	6.10 × 10 ⁴
HFSPURE	6		1584		1.83	676	1.43 × 10 ⁴	28.69 × 10 ⁴
			15114		2.64	979	2.07 × 10 ⁴	81.74 × 10 ⁴
		5	8516		0.23	83	0.05 × 10 ⁴	0.24 × 10 ⁴
		6	1220		0.33	121	0.17 × 10 ⁴	0.58 × 10 ⁴
		8	1830		0.98	361	1.12 × 10 ⁴	3.65 × 10 ⁴

Delivery 天发货
数量分类 标准订购 特殊订购
数量 1～50 51～
交货期 通常 另行报价

遇特殊期间交期有变更，详情请见 P.9。



通用铝合金型材




CAD数据文件名: 37_Aluminum_Frames


请按照选型步骤①～⑥选择型式和参数后进行订购。

Order 型式 (①Type · ②A · ③B) - ④T - ⑤L
订货范例 HFHL3030 - 3 - 800


■槽型



型式	①Type	②A	③B	④T	⑤L 指定単位1mm	質量 kg/m	截面積 mm ²	截面慣性矩	
								ℓx × 10 ⁴	ℓy × 10 ⁴
HFHC (槽型)	2	15	15	50～2000		0.222	82	0.1433	0.227
		20	20			0.304	112	0.232	1.471
		20	40			0.304	112	0.453	0.719
		25	25			0.412	152	0.576	3.668
			50			0.381	142	1.479	0.911
						0.761	282	1.640	10.42



■L型



型式	①Type	②A	③B	④T	⑤L 指定単位1mm	質量 kg/m	截面積 mm ²	截面慣性矩	
								ℓx × 10 ⁴	ℓy × 10 ⁴
HFHL (L型)	20	20	2	50～2000		0.206	76	0.288	0.288
			3			0.301	111	0.403	0.403
			2			0.315	116	0.348	1.964
			3			0.464	171	0.489	2.82
		25	2			0.381	141	0.819	0.819
			3			0.583	216	0.993	5.661
	30	30	2			0.315	116	1.019	1.019
			3			0.464	171	1.458	1.458
			5			0.745	275	2.21	2.21
			2			0.412	156	2.47	2.47
		40	3			0.626	231	3.58	3.58
			5			1.016	375	5.56	5.56
	50	50	3			0.785	291	7.15	7.15

Delivery 天发货
数量分类 标准订购 特殊订购
数量 1～50 51～
交货期 通常 另行报价

